

Product data sheet

Characteristics

EZMR333225

Branch unit, EZ Meter-Pak, 225A, 3 x 7 jaw sockets, 208Y/120VAC, no bypass, ringless, 1200A Al/Cu busbar



Main

| | |
|-------------------------|--------------------------|
| Product | Meter Center Branch Unit |
| Current Rating | 225 A |
| Type | Meter-Pak |
| Bus Rating | 1200 A |
| Number of Jaws | 7 without jaw release |
| Number of Meter Sockets | 3 |
| Bypass Type | No bypass |
| Socket Type | Ringless |

Complementary

| | |
|------------------------|-------------------------------------|
| Certifications | UL Listed |
| Busbar Material | Aluminium/copper: busbar |
| Enclosure Material | Steel |
| Enclosure Rating | NEMA 3R |
| Maximum Voltage Rating | 208Y/120 V AC 240/120 V delta AC |
| Mounting | Surface |
| Phase | 3 phase in 3 phase out |
| Wire Configuration | 4-wire |
| Height | 53.06 in (1347.72 mm) |
| Width | 19.44 in (493.78 mm) |
| Depth | 9.44 in (239.78 mm) |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10DE400020 |
| Discount Schedule | ODE4 |
| GTIN | 785901337942 |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------------------|---------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 11.50 in (29.2 cm) |
| Package 1 Width | 21.50 in (54.6 cm) |
| Package 1 Length | 54.02 in (137.2 cm) |
| Package 1 Weight | 160.00 lb(US) (72.575 kg) |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|