



Main

Range	TeSys
Product or Component Type	Enclosure
Device short name	GV2MC
Accessory / separate part category	Mounting accessory
Product Compatibility	GV2ME
Enclosure type	Surface mounting

Complementary

Auxiliary mounting location	Left Right
Height	5.79 in (147 mm)
Width	3.66 in (93 mm)
Depth	3.31 in (84 mm)
Net Weight	0.66 lb(US) (0.3 kg)

Environment

IP degree of protection	IP55
Environmental characteristic	Standard environment
Product Certifications	UKCA

Ordering and shipping details

Category	22367-MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	3389110213652
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.94 in (10.000 cm)
Package 1 Width	3.94 in (10.000 cm)
Package 1 Length	6.10 in (15.500 cm)
Package 1 Weight	10.37 oz (294.000 g)
Unit Type of Package 2	S04
Number of Units in Package 2	27
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	15.75 in (40.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	19.10 lb(US) (8.662 kg)
Unit Type of Package 3	P06

Number of Units in Package 3	108
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	100.97 lb(US) (45.800 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------