

# H362N

Safety switch, heavy duty, fusible, 60A, 3 poles, 50 hp, 600 VAC/DC, neutral factory installed, NEMA1



## Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Fusible disconnect
Factory Installed Neutral	Neutral (factory installed)
Phase	3 phase
Number of Poles	3
Current Rating	60 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 1 steel
Maximum Horse Power Rating	15 Hp 480 V at AC 50-60 Hz for 3 phase conforming to NEC 240.6 30 Hp 480 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52 15 Hp 600 V at AC 50-60 Hz for 3 phase conforming to NEC 240.6 50 Hp 600 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52 30 hp 600 V at DC

## Complementary

Short Circuit Current Rating	10 KA H or K 200 kA R or J
Fuse type	H or K R or J
Mounting Type	Surface
Electrical Connection	Lugs
Wiring configuration	4-wire (3PH + N)
Wire Size	AWG 14...AWG 3 copper AWG 12...AWG 3 aluminium
Tightening torque	50 Lbf.In (5.65 N.m) (AWG 3) 45 Lbf.In (5.08 N.m) (AWG 6...AWG 4) 40 Lbf.In (4.52 N.m) 0.01 in <sup>2</sup> (8.367 mm <sup>2</sup> ) (AWG 8) 50 lbf.in (5.65 N.m) 0.00...0.01 in <sup>2</sup> (2.06...5.261 mm <sup>2</sup> ) (AWG 14...AWG 10)
Depth	6.38 in (162.05 mm)
Width	10.5 in (266.70 mm)
Height	17.5 in (444.50 mm)
Net Weight	15.43 lb(US) (7 kg)

## Environment

Certifications	UL listed file E2875
----------------	----------------------

## Ordering and shipping details

Category	00008 - H&HU SW,2&3P,N1,30-200A
Discount Schedule	DE1
GTIN	785901482215
Nbr. of units in pkg.	1
Package weight(Lbs)	15.30 lb(US) (6.94 kg)

Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	7.40 in (18.796 cm)
Package 1 width	10.80 in (27.432 cm)
Package 1 Length	19.80 in (50.292 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	40
Package 2 Weight	648.00 lb(US) (293.928 kg)
Package 2 Height	41.50 in (105.41 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

