



Main

Range	TeSys
Device short name	LUFN
Product or Component Type	Auxiliary contact

Complementary

Auxiliary contact composition	1 NO + 1 NC
[Ue] rated operational voltage	<= 250 V AC <= 250 V DC
[Ui] rated insulation voltage	250 V CSA 250 V IEC 60947-5-1 250 V UL
[Ith] conventional free air thermal current	5 A
Minimum switching voltage	17 V
Minimum switching current	5 mA
Net Weight	0.11 lb(US) (0.05 kg)

Ordering and shipping details

Category	22399-TESYS U, ACCESSORIES
Discount Schedule	I11
GTIN	3389110365177
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	1.30 in (3.3 cm)
Package 1 Length	1.89 in (4.8 cm)
Package 1 Weight	1.62 oz (46.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	60
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	6.85 lb(US) (3.108 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------