

M800S

TYPE 1 300 to 800A SURFACE MOUNT MOULDED CASE CIRCUIT BREAKER ENCLOSURE



Main

| | |
|----------------------|--|
| Circuit Breaker Type | PKL PJL MGL PGL MJL PLL |
| Product Destination | Circuit breaker M 3P Circuit breaker P 2P |

Complementary

| | |
|--------------------|-----------------------|
| Enclosure Material | Steel |
| Width | 21.00 in (533.4 mm) |
| Height | 40.37 in (1025.52 mm) |
| Depth | 9.75 in (247.65 mm) |
| Rated Current | 300...800 A |
| Device Mounting | Surface |
| Poles Description | 3P 2P |

Environment

| | |
|------------------------|-----------|
| Product Certifications | CSA UL |
|------------------------|-----------|

Environmental

| | |
|---------------------------|--------|
| NEMA Degree of Protection | NEMA 1 |
| NEMA Degree of Protection | NEMA 1 |

Ordering and shipping details

| | |
|-----------------------|-------------------------------|
| Category | 00030 - IND CB ENCL NEMA 1,3R |
| Discount Schedule | DE1 |
| GTIN | 785901430438 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 95.46 lb(US) (43.3 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------|---------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 13.19 in (33.5 cm) |
| Package 1 width | 22.72 in (57.7 cm) |
| Package 1 Length | 42.01 in (106.7 cm) |

Offer Sustainability

| | |
|-----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| PVC free | Yes |
| Halogen content performance | Halogen free plastic parts product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|