



## Main

Range	Spacial
Product name	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	27.56 in (700 mm)
Enclosure nominal width	19.69 in (500 mm)
Enclosure nominal depth	9.84 in (250 mm)
Installation accessory type	Wall-mounting
Device composition	1 body 1 cable gland plate 1 door with lock 1 mounting plate
Door type	Solid
Mounting plate description	Plain

## Complementary

Body type	Back welded with double profile forming a protected sealed area Sides made from a single folded section
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure steel Mounting plate galvanised steel
Surface finish	Enclosure epoxy-polyester powder
Color	Enclosure Gray RAL 7035)
Standards	IEC 62208
Product Certifications	CUL UL DNV-GL
Net Weight	44.74 lb(US) (20.292 kg)

## Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262

## Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480211874
Returnability	No
Country of origin	ES

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	10.43 in (26.5 cm)
Package 1 Width	19.88 in (50.5 cm)
Package 1 Length	27.95 in (71 cm)
Package 1 Weight	46.61 lb(US) (21.141 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------