



Main

Circuit Breaker Type	QDL QBL QJL QGL
Product Destination	Circuit breaker QB/QD/QJ/QL 3P Circuit breaker QB/QD/QJ/QL 2P

Complementary

Enclosure Material	Steel
Width	9.88 in (251 mm)
Height	26.26 in (667 mm)
Depth	5.51 in (140 mm)
Rated Voltage	240 V AC
Rated Current	100...225 A
Poles Description	2P 3P
Tightening Torque	247.82 lbf.in (28 N.m) (AWG 4...300 kcmil)

Environment

Product Certifications	UL
------------------------	----

Environmental

NEMA Degree of Protection	NEMA 3R
NEMA Degree of Protection	NEMA 3R

Ordering and shipping details

Category	00023 - QO,Q2L 3P ENCL & BREAKERS
Discount Schedule	DE2
GTIN	785901470625
Nbr. of units in pkg.	1
Package weight(Lbs)	22.18 lb(US) (10.06 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.00 in (15.24 cm)
Package 1 width	11.00 in (27.94 cm)
Package 1 Length	27.70 in (70.358 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------