



Main

| | |
|---------------------------|------------------|
| Product or Component Type | Circuit breaker |
| Trip Unit Technology | Thermal-magnetic |

Complementary

| | |
|---------------------------|--|
| Line Rated Current | 250 A |
| Number of Poles | 3P |
| Breaking capacity code | Q4 |
| Mounting Mode | Unit mount |
| Magnetic Hold Current | 1250 A |
| Magnetic Tripping Current | 2500 A |
| Electrical connection | Lugs load Lugs line |
| Terminal identifier | AL400LA |
| Tightening torque | 371.73 Lbf.in (42 N.m) 0.08...0.47 in ² (50...300 mm ²) (AWG 1...600 kcmil) 371.73 lbf.in (42 N.m) 0.08...0.19 in ² (50...120 mm ²) (AWG 1...250 kcmil) |
| Height | 11 in (279.40 mm) |
| Width | 6 in (152.40 mm) |
| Depth | 5.84 in (148.34 mm) |

Environment

| | |
|----------------|-------------------------|
| Certifications | CSA IEC UL Listed |
|----------------|-------------------------|

Ordering and shipping details

| | |
|-------------------|----------------------------|
| Category | 00933-Q4L BREAKER & SWITCH |
| Discount Schedule | DE2 |
| GTIN | 785901649250 |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|-----------------------|
| Unit Type of Package 1 | Db |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.09 in (23.1 cm) |
| Package 1 Width | 11.61 in (29.5 cm) |
| Package 1 Length | 17.28 in (43.9 cm) |
| Package 1 Weight | 16.31 lb(US) (7.4 kg) |

Offer Sustainability

| | |
|-----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| PVC free | Yes |
| Halogen content performance | Halogen free plastic parts product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|