



Main

Product or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

Line Rated Current	400 A
Number of Poles	3P
Breaking capacity code	Q4
Mounting Mode	Unit mount
Magnetic Hold Current	2000 A
Magnetic Tripping Current	4000 A
Electrical connection	Lugs, load Lugs, line
Terminal identifier	AL400LA
Tightening torque	371.7 Lbf.in (42 N.m) 0.08...0.5 in ² (50...300 mm ²) (AWG 1...600 kcmil) 371.7 lbf.in (42 N.m) 0.08...0.2 in ² (50...120 mm ²) (AWG 1...250 kcmil)
Height	11 in (279.4 mm)
Width	6 in (152.4 mm)
Depth	5.84 in (148.34 mm)

Environment

Certifications	IEC[RETURN]UL Listed[RETURN]CSA
----------------	---------------------------------

Ordering and shipping details

Category	US10DE200933
Discount Schedule	0DE2
GTIN	785901649281
Returnability	Yes
Country of origin	IE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.9 in (22.6 cm)
Package 1 Width	11.4 in (29.0 cm)
Package 1 Length	17.4 in (44.2 cm)
Package 1 Weight	16.38 lb(US) (7.43 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------