



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	60 A
Voltage Rating	120/240 V AC 120 V AC 48 V DC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	10 KA 120/240 V AC 50/60 Hz 10 KA 120 V AC 50/60 Hz 5 kA 48 V DC
Number of Panel Spaces	1
Wire Size	AWG 8...AWG 2 copper or aluminium
Tightening Torque	44.25 lbf.in (5 N.m) 0.02...0.04 in ² (10...25 mm ²) (AWG 8...AWG 2)
Height	3.11 in (79 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.31 lb(US) (0.141 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00104 - QO 35-70A 1P;70-125A 2P CB
Discount Schedule	DE2A
GTIN	785901477464
Nbr. of units in pkg.	96
Package weight(Lbs)	96 lb(US) (43.54 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	0.70 in (1.778 cm)
Package 1 width	3.50 in (8.890 cm)
Package 1 Length	3.50 in (8.890 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------