



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	30 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Pressure plate

Complementary

Interrupt Rating	10 KA 120/240 V AC 10 kA 120 V AC
Number of Panel Spaces	2
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Tightening Torque	35.4 Lbf.in (4 N.m) 40.7 lbf.in (4.6 N.m) 0.006...0.03 in ² (4...20 mm ²) (AWG 12...AWG 4)
Height	4.1 in (105 mm)
Width	1.5 in (38 mm)
Depth	2.9 in (74 mm)
Net Weight	0.721 lb(US) (0.327 kg)

Environment

Certifications	UL Listed[RETURN]CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US1DE2A00003
Discount Schedule	DE2A
GTIN	785901563006
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.600 in (9.144 cm)
Package 1 Width	2.200 in (5.588 cm)
Package 1 Length	5.400 in (13.716 cm)
Package 1 Weight	15.20 oz (430.91 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	33

Package 2 Height	5.50 in (13.97 cm)
Package 2 Width	13.600 in (34.544 cm)
Package 2 Length	20.900 in (53.086 cm)
Package 2 Weight	32.119 lb(US) (14.569 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------