

Product data sheet

Characteristics

QO320GFI

Mini circuit breaker, QO, 20A, 3 pole,
208Y/120VAC, 10kA, 6mA grd fault A, pigtail,
plug in mount



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	208Y/120 V AC
Mounting Type	Plug-in
Number of Poles	3P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Pressure plate

Complementary

Interrupt Rating	10 kA 208Y/120 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Tightening Torque	40.71 Lbf.in (4.6 N.m) 0.00...0.02 in ² (2.5...10 mm ²) (AWG 16...AWG 14) 40.71 lbf.in (4.6 N.m) 0.01...0.03 in ² (4...20 mm ²) (AWG 12...AWG 4)
Height	4.13 in (105 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	1.32 lb(US) (0.600 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00103-QO 2 POLE GFI CB 40-60A
Discount Schedule	DE2A
GTIN	785901298588
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.70 in (6.858 cm)
Package 1 Width	3.40 in (8.636 cm)
Package 1 Length	6.50 in (16.51 cm)
Package 1 Weight	1.32 lb(US) (0.6 kg)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------