



## Main

Marketing Trade Name	QO
Product Type	Load Center
Cover Type	Order separately

## Complementary

Tightening Torque	Main lugs 250 lb.in, AWG 4...250 kcmil, aluminium/copper Cover 20 lb.in
PoN Convertible Mains (lugs)	Fixed Mains (lugs)
Rated Current	225 A
Number of Spaces	42
Max Short Circuit Current Rating	65 kA
Maximum Number of Single Pole Circuits	42
Maximum Number of Tandem Breakers	0
Number of Phases	3 phase
Voltage Rating	208Y/120 V AC 240/120 V delta AC 240 V delta AC
Wire Size	AWG 6...300 kcmil aluminium/copper
Ground Bar	Grounding bar included (not installed)
Electrical Connection	Lugs
Wiring Configuration	3-wire 4-wire
Busbar Material	Tin plated copper busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel Gray
Box Number	11
Height	37.99 in (965 mm)
Width	14.25 in (362 mm)

## Environment

Enclosure Rating	NEMA 1 indoor
Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL Listed

## Ordering and shipping details

Category	00011-QO 3PH LOAD CENTER,INDOOR
Discount Schedule	DE3
GTIN	785901295532
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	39.00 in (99.06 cm)
Package 1 Width	4.30 in (10.922 cm)
Package 1 Length	14.80 in (37.592 cm)
Package 1 Weight	20.70 lb(US) (9.389 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	27
Package 2 Height	42.00 in (106.68 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	565.89 lb(US) (256.685 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------