



## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	80 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Plug-in
Number of Poles	3P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

## Complementary

Interrupt Rating	10 KA 120/240 V AC 50/60 Hz 10 KA 240 V AC 50/60 Hz 10 kA 120 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 4...AWG 2/0 copper or aluminium
Tightening Torque	44.25 lbf.in (5 N.m) 0.02...0.04 in <sup>2</sup> (10...25 mm <sup>2</sup> ) (AWG 8...AWG 2)
Height	3.50 in (89 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	1.07 lb(US) (0.485 kg)

## Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00012-QO 3 POLE CIRCUIT BREAKER
Discount Schedule	DE2A
GTIN	785901004394
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	2.20 in (5.588 cm)
Package 1 Width	3.40 in (8.636 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	17.11 oz (485 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Height	3.80 in (9.652 cm)
Package 2 Width	13.90 in (35.306 cm)

Package 2 Length	21.00 in (53.34 cm)
Package 2 Weight	39.25 lb(US) (17.803 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	1728
Package 3 Height	40.00 in (101.6 cm)
Package 3 Width	36.00 in (91.44 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	1848.96 lb(US) (838.673 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Halogen content performance	Halogen free product

### Contractual warranty

Warranty	18 months
----------	-----------