



## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	60 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs

## Complementary

Interrupt Rating	22 KA 120/240 V AC 50/60 Hz 22 KA 240 V AC 50/60 Hz 22 kA 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 8...AWG 2 copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	3.11 in (79 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.74 lb(US) (0.336 kg)

## Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00015-QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	785901054788
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	1.50 in (3.81 cm)
Package 1 Width	3.40 in (8.636 cm)
Package 1 Length	3.80 in (9.652 cm)
Package 1 Weight	11.84 oz (335.658 g)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------