



## Main

|                      |                   |
|----------------------|-------------------|
| Marketing Trade Name | QO                |
| Product Type         | Load Center Cover |

## Complementary

|                       |                        |
|-----------------------|------------------------|
| Cover Type            | Surface cover          |
| Product Compatibility | For indoor load center |
| Surface Finish        | Baked enamel Gray      |
| Number of Spaces      | 16                     |
| Height                | 17.92 in (455.17 mm)   |
| Width                 | 14.24 in (361.70 mm)   |
| Depth                 | 0.7 in (17.78 mm)      |
| Tightening Torque     | Cover 2.3 N.m          |

## Ordering and shipping details

|                       |                                 |
|-----------------------|---------------------------------|
| Category              | 00001-QO 1PH LC,12-42 CKT,NEMA1 |
| Discount Schedule     | DE3A                            |
| GTIN                  | 785901745990                    |
| Nbr. of units in pkg. | 1                               |
| Package weight(Lbs)   | 5.85 lb(US) (2.654 kg)          |
| Returnability         | Yes                             |
| Country of origin     | US                              |

## Packing Units

|                              |                            |
|------------------------------|----------------------------|
| Unit Type of Package 1       | PCE                        |
| Package 1 Height             | 0.70 in (1.78 cm)          |
| Package 1 width              | 14.24 in (36.17 cm)        |
| Package 1 Length             | 17.92 in (45.52 cm)        |
| Unit Type of Package 2       | PAL                        |
| Number of Units in Package 2 | 162                        |
| Package 2 Weight             | 946.00 lb(US) (429.098 kg) |
| Package 2 Height             | 39.50 in (100.33 cm)       |
| Package 2 width              | 40.00 in (101.6 cm)        |
| Package 2 Length             | 48.00 in (121.92 cm)       |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|