



Main

Product	Circuit breaker
Range	QO
Current Rating	100 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Bolt-on
Number of Poles	2P

Complementary

Interrupt Rating	22 kA 120/240 V AC 50/60 Hz 22 kA 120 V AC 50/60 Hz
Tightening Torque	53.10 lbf.in (6 N.m) 0.01...0.10 in ² (4...65 mm ²) (AWG 12...AWG 2/0)
Net Weight	1.40 lb(US) (0.635 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00100 - QOM-VH MAIN CB
Discount Schedule	DE3A
GTIN	785901004035
Nbr. of units in pkg.	1
Package weight(Lbs)	1.4 lb(US) (0.64 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.20 in (10.668 cm)
Package 1 width	4.40 in (11.176 cm)
Package 1 Length	5.30 in (13.462 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	621
Package 2 Weight	829.88 lb(US) (376.427 kg)
Package 2 Height	40.00 in (101.6 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------