

SSP01EMA24

Surge protection device, Surgelogic, 240kA,
120/240 VAC, 1 phase, 3 wire, NEMA 1



Main

Product	Surge protection device
Range	Surgelogic
Device Short Name	EMA

Complementary

Surge Current	240 kA
Voltage Rating	120/240 V AC
Number of Phases	1 phase
Wiring Configuration	3-wire
Connection	Lugs AWG 10...AWG 2 copper 35.40 lbf.in (4 N.m)
MCOV	150 V
Nominal Discharge Current	20 kA
SCCR	200 kA
Local Signalling	Status LED green per phase normal operation Status LED red per phase fault
Provided Equipment	Alarm enable/disable switch Surge counter Dry contacts
Device Mounting	Surface
Height	11.10 in (282 mm)
Width	9.98 in (253.5 mm)
Depth	5.31 in (135 mm)
Cable length	19.02 in (483 mm)

Environment

Enclosure Rating	NEMA 1
Enclosure Material	Gray painted sheet steel
Standards	CSA C22.2 No 8 UL 1449:ed. 4 UL 1283:ed. 5
Ambient Operating	149 °F (65 °C)

Ordering and shipping details

Category	08464-SURGE PROTECTION EMA
Discount Schedule	DE1B
GTIN	785901957874
Nbr. of units in pkg.	1
Package weight(Lbs)	20.50 lb(US) (9.299 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	11.10 in (28.2 cm)
Package 1 width	10.00 in (25.4 cm)
Package 1 Length	5.31 in (13.5 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration