



Main

Range of Product	Altivar
Range compatibility	Altivar&Nbsp;Process ATV900 Altivar&Nbsp;Process ATV600 Altivar Machine ATV340
Accessory / separate part category	Display and signalling accessories
Accessory / separate part type	Display terminal
Accessory / separate part destination	Variable speed drive
Product Specific Application	To control, adjust and configure the drive To save and download configurations To display the current values
IP Degree of Protection	IP65

Complementary

User Language	Spanish Romanian Turkish Polish Swedish Estonian Bulgarian English Russian Greek Danish Hungarian Chinese Norwegian Lituanien French Brazilian German Korean Portuguese Finnish Czech Slovak Taiwanese Dutch Italian
Realtime clock	Built-in
Battery Size	CR2032
Battery Life	10 year(s)
Display type	Backlit LCD screen white and red
Messages display capacity	8 lines
Pixel resolution	240 x 160
Net Weight	0.44 lb(US) (0.2 kg)

Environment

Ambient air temperature for operation	5...122 °F (-15...50 °C)
---------------------------------------	--------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22205-ATV630 FRAMES 1 & 2
Discount Schedule	CP4E
GTIN	3606480702235
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.24 in (5.7 cm)
Package 1 Width	5.39 in (13.7 cm)
Package 1 Length	7.32 in (18.6 cm)
Package 1 Weight	9.31 oz (264.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	20
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	13.38 lb(US) (6.069 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	80
Package 3 Height	17.72 in (45.0 cm)
Package 3 Width	23.62 in (60.0 cm)
Package 3 Length	31.50 in (80.0 cm)
Package 3 Weight	72.26 lb(US) (32.776 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes