



### Main

Range	TeSys
Device short name	VZ
Product or Component Type	Auxiliary contact block
Performance level	High performance
Contacts type and composition	1 NO + 1 NO
Product Compatibility	V3 V01 V2 V0 V6 V4 V1 V5 V02
Network type	DC AC
Network Frequency	50/60 Hz
Mounting Location	Left Right

### Complementary

[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	12 A
[Ithe] conventional enclosed thermal current	10 A
Mechanical durability	100000 cycles
Electrical durability	30000 Cycles DC-11 100000 cycles AC-15
Connections - terminals	Screw clamp terminals 2 0.00...0.00 in <sup>2</sup> (0.75...1.5 mm <sup>2</sup> ) flexible - with cable end Screw clamp terminals 2 0.00...0.00 in <sup>2</sup> (1...2.5 mm <sup>2</sup> ) solid
Tightening torque	6.20 lbf.in (0.7 N.m) screw clamp terminals
Height	2.56 in (65 mm)
Width	0.79 in (20 mm)
Depth	1.91 in (48.5 mm)
Net Weight	0.11 lb(US) (0.05 kg)

### Environment

Standards	IEC 60947-5
Product Certifications	GL[RETURN]UL[RETURN]CSA[RETURN]UKCA
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Ordering and shipping details

Category	US10CP121730
Discount Schedule	0CP1
GTIN	3389110551976
Returnability	Yes
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.38 in (3.500 cm)
Package 1 Width	2.17 in (5.500 cm)
Package 1 Length	3.54 in (9.000 cm)
Package 1 Weight	1.92 oz (54.400 g)
Unit Type of Package 2	S02
Number of Units in Package 2	69
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	8.82 lb(US) (4.001 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------