

# Product data sheet

## Characteristics

# 2420100

## Insulation tape, Thorsman, 19mm x 20m, red



### Main

|                           |  |
|---------------------------|--|
| Range of product          | Thorsman   |
| Range                     | Thorsman   |
| Product or component type | Insulation tape  |
| Device application        | General work<br>Colour coding<br>Binding<br>Insulation |
| Material                  | PVC (polyvinyl chloride)                               |
| Standards                 | BS EN 60454  |

### Complementary

|                                       |                    |
|---------------------------------------|--------------------|
| Colour                                | Red                |
| Length                                | 20 m               |
| Width                                 | 19 mm              |
| Thickness                             | 0.13 mm            |
| Flame retardance                      | Self-extinguishing |
| Ambient air temperature for operation | 0...90 °C          |

### Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 2.000 cm   |
| Package 1 Width              | 6.500 cm   |
| Package 1 Length             | 6.500 cm   |
| Package 1 Weight             | 65.000 g   |
| Unit Type of Package 2       | S04        |
| Number of Units in Package 2 | 200        |
| Package 2 Height             | 30.000 cm  |
| Package 2 Width              | 40.000 cm  |
| Package 2 Length             | 60.000 cm  |
| Package 2 Weight             | 14.180 kg  |
| Unit Type of Package 3       | P12        |
| Number of Units in Package 3 | 6000       |
| Package 3 Height             | 160.000 cm |
| Package 3 Width              | 80.000 cm  |
| Package 3 Length             | 120.000 cm |
| Package 3 Weight             | 437.400 kg |

### Offer Sustainability

|                        |  |
|------------------------|--|
| RECh Regulation        | <a href="#">RECh Declaration</a>   |
| RECh free of SVHC      | Yes  |
| EU RoHS Directive      | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free | Yes  |
| Mercury free           | Yes  |

|                            |  |
|----------------------------|--|
| Sustainable packaging      | Yes                                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a> |
| RoHS exemption information | <a href="#">Yes</a>                    |