

Product data sheet

Characteristics

9001KS53FBH2

Selector switch, Harmony 9001K, metal, long handle, black, 30mm, 3 positions, return both sides to center, 2 C/O



Main

Range of product	Harmony 9001K
Product or component type	Selector switch
Device short name	K
Type of operator	Spring return
Operator profile	Black gloved hand knob

Complementary

Bezel material	Metal
Mounting diameter	30 mm
Operator position information	3 positions
Contacts type and composition	2 C/O
Connections - terminals	Screw-clamp terminals, 1 x 0.22...2 x 1.5 mm ² conforming to IEC 60947-1
Device presentation	Complete product
Cap/operator or lens colour	Black
Operator profile	Long handle
Type of operator	Spring return
Size	30 mm
Return	Both sides to centre
Cam profile	3

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CSA LR24590 class 3211 03[RETURN]CE[RETURN]UL listed file E42259 CCN NKCR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	9.5 cm
Package 1 Length	5.7 cm
Package 1 Weight	176.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.442 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	"WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "