



### Main

|                           |  |
|---------------------------|--|
| Range of the product      | Acti9 Disbo  |
| Product or component type | Distribution board with incomer  |
| Enclosure type            | Distribution enclosure   |
| Device application        | Low voltage electrical distribution  |
| Provided equipment        | Molded case circuit breaker (MCCB)<br>Pan assembly<br>Earthing bar<br>Neutral bar<br>enclosure |
| Number of ways            | 36 ways (outgoer)  |

### Complementary

|  |  |
|--|--|
| [In] rated current                       | 200 A  |
| [Icw] rated short-time withstand current | 25 kA for 0.3 s  |
| [Ipk] rated peak withstand current       | 52.5 kA  |
| [Uimp] rated impulse withstand voltage   | 6 kV   |
| Rated voltage                            | 220...440 V AC 50/60 Hz  |
| Network number of phases                 | 3 phases 4 wires   |
| [Ui] rated insulation voltage            | 690 V AC   |
| Protection device options                | Molded case circuit breaker (MCCB) (incomer)<br>Miniature circuit breaker (MCB) (outgoer)<br>Residual current circuit breaker with overcurrent protection (RCBO) (outgoer) |
| Enclosure mounting                       | Flush  |
| Door type                                | Plain flat door  |
| Cable entry                              | Removable gland plate at top and bottom of the enclosure   |
| Enclosure material                       | Painted sheet steel  |
| Colour                                   | White (RAL 9003)   |
| Width                                    | Outside: 440 mm<br>Embedded: 400 mm  |
| Height                                   | Outside: 888.3 mm<br>Embedded: 852.4 mm  |
| Depth                                    | Outside : 138.2 mm<br>Embedded : 134.5 mm  |

### Environment

|                                       |                              |
|---------------------------------------|------------------------------|
| IP degree of protection               | IP40 conforming to IEC 60529 |
| Ambient air temperature for operation | 50 °C                        |
| Standards                             | IEC 61439-3                  |
| Product certifications                | ASTA[RETURN]SASO             |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 13.9 cm  |
| Package 1 Width              | 44.0 cm  |
| Package 1 Length             | 88.83 cm |
| Package 1 Weight             | 23.31 kg |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product                                      |
| REACH Regulation           | <a href="#">REACH Declaration</a>                          |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) |
| Sustainable packaging      | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                     |
| RoHS exemption information | <a href="#">Yes</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>              |
| Circularity Profile        | No need of specific recycling operations                   |