

Main

Range of the product	Acti9 Disbo
Product or component type	Distribution board
Enclosure type	Row Disbo
Device application	Low voltage electrical distribution
Number of horizontal rows	5
Provided equipment	Enclosure DIN rail

Complementary

Number of 18 mm modules per row	80
[In] rated current	125 A
Rated voltage	220...440 V AC 50/60 Hz
[Ui] rated insulation voltage	690 V AC
Protection device options	Isolator 125 A max as incomer Miniature circuit breaker (MCB) 125 A max as incomer RCCB 125 A max as incomer Residual current circuit breaker with overcurrent protection (RCBO) 63 A max as outgoer Miniature circuit breaker (MCB) 63 A max as outgoer
Enclosure mounting	Surface
Door type	Plain flat door
Type of rail	DIN
Cable entry	Removable gland plate at top and bottom of the enclosure
Enclosure material	Electro galvanised steel
Colour	White (RAL 9003)
Width	400 mm
Height	1000 mm
Depth	117 mm

Environment

IP degree of protection	IP40 conforming to IEC 60529
Ambient air temperature for operation	50 °C
Standards	IEC 61439-3

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.7 cm
Package 1 Width	40.0 cm
Package 1 Length	100.0 cm
Package 1 Weight	16.4 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No