



Main

Range of product	Twido
Accessory / separate part designation	Discrete input pre-formed cable
Accessory / separate part type	Connecting cable
Accessory / separate part category	Connection accessories
Accessory / separate part destination	Discrete input
Product specific application	For application other than use of Advantys Telefast ABE7 sub-base

Complementary

Product compatibility	TWDDDI32DK TWDDDI16DK
Cable length	3 m
AWG gauge	AWG 28
Cable cross section	0.08 mm ²
Electrical connection	1 connector HE10 20 pin(s) sensor side 1 connector HE10 20 pin(s) Twido side
Net weight	0.21 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm
Package 1 Width	20 cm
Package 1 Length	16 cm
Package 1 Weight	192 g
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.255 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------
