



### Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	LED lighting: : 100 W Incandescent lamps: : 2000 W - 230 V Halogen lamp: : 1000 W - 230 V Halogen lamp with standard electronic transformer: 1000 VA Halogen lamp with standard ferromagnetic transformer: 1000 VA Fluorescent tube: 900 VA, 100 µF
Colour tint	White

### Complementary

Network frequency	50/60 Hz
Input function	Switch External trigger
Output voltage	220...250 V
Output current	10 A
Number of channels	2
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	10...1000 lux
Horizontal detection angle	360 °
Mounting height	2.5 m






### Environment

IP degree of protection	IP20
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.2 cm
Package 1 Width	11.7 cm
Package 1 Length	17.7 cm
Package 1 Weight	462 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	40 cm
Package 2 Width	31 cm
Package 2 Length	50 cm
Package 2 Weight	10.29 kg
Unit Type of Package 3	P12
Number of Units in Package 3	160
Package 3 Height	95 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	88.92 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	<a href="#"> End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins