



Main

Range of product	DA1
Product or component type	Thermistor probe
Device short name	DA1TT
Accessory / separate part category	Protection accessory
Quantity per set	Set of 10
Ambient air temperature for operation	90 °C

Complementary

[Ui] rated insulation voltage	2500 V
[Ue] rated operational voltage	<= 2.5 V
Resistance	250 Ohm per probe 25 °C
Insulation	Reinforced
Cable length	1 m between probe and motor terminal plate
Net weight	0.01 kg

Environment

Standards	IEC 60034-11 Mark A
-----------	---------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.100 cm
Package 1 Width	12.000 cm
Package 1 Length	15.000 cm
Package 1 Weight	9.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	2.000 cm
Package 2 Width	12.000 cm
Package 2 Length	16.000 cm
Package 2 Weight	96.000 g
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.152 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------