

### Main

Range of the product	Disbo Extra
Enclosure type	Distribution enclosure
Device short name	distribution enclosure
Accessories included with enclosure	Incoming device Metal enclosure Template Front cover Multi function packing box Pan assembly Cement spill protection carton
Number of ways	36 ways

### Complementary

[In] rated current	80 A
[Icw] rated short-time withstand current	17 kA for 0.2 s
[Ipk] rated peak withstand current	34 kA
Enclosure mounting	Flush
Locking options description	Keylock option
Enclosure material	Zinc coated metal sheet
Incomer device	NS100N - 3P
Width	440 mm
Height	890 mm
Depth	149 mm

### Environment

IP degree of protection	IP31 conforming to IEC 60529
Standards	IEC 60947-2 IEC 60947-1 IEC 60439-3

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

### Contractual warranty

Warranty	18 months
----------	-----------