



### Main

Product or component type	USB charger
Fixing mode	Screw

### Complementary

Device mounting	Flush
Device presentation	Mechanism
Colour tint	Lavender silver
Surface finish	Glossy
Surface treatment	Untreated
Number of modules	1 module 46 x 36.7 x 21.7 mm
Condition of use	Room temperature
Ambient air temperature for storage	-5...60 °C
Relative humidity	10...90 %
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Integrated connection type	1 USB port 5 V DC, maximum load current: 2.1 A
Material	Silicone rubber: cover PC (polycarbonate): grid plate PC (polycarbonate): housing
Shape of screw head	Cross
Number of terminals	2 screw terminals
Clamping connection capacity	2.5 mm <sup>2</sup> for stranded cable(s) 2.5 mm <sup>2</sup> for flexible cable(s) 2.5 mm <sup>2</sup> for rigid cable(s) 1.5 mm <sup>2</sup> for stranded cable(s) 1.5 mm <sup>2</sup> for flexible cable(s) 1.5 mm <sup>2</sup> for rigid cable(s)
Wire stripping length	6 mm
Product compatibility	HW Samsung Major smart phone and tablet XiaoMi Apple HTC Power bank
Standards	CNS 14336 MS IEC 60950-1 GB 4943.1 IEC 60950-1 CNS 13438
Height	87 mm
Width	87 mm
Depth	39 mm

Embedding depth	27.3 mm
Net weight	0.0767 kg

## Environment

Product certifications	IEC[RETURN]CCC
IP degree of protection	IP20
Environmental characteristic	Liquid soap Alcohol

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	83 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	664 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6680 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>