

Main

Range	Lineryg
Product name	FT
Device short name	GV1G
Product or component type	Terminal block
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys GV2 TeSys Deca TeSys U TeSys LS1

Complementary

[Ie] rated operational current	63 A
Mounting location	Top
IP degree of protection	IP20 conforming to IEC 60529
[Ui] rated insulation voltage	690 V conforming to IEC 60947-1
Connections - terminals	Screw clamp terminals 1 solid AWG 4 Screw clamp terminals 1 cable(s) 1.5...16 mm ² flexible with cable end Screw clamp terminals 1 cable(s) 1.5...16 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 1.5...25 mm ² solid Screw clamp terminals 2 cable(s) 1.5...4 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 1.5...6 mm ² solid Screw clamp terminals 2 cable(s) 1.5...4 mm ² flexible without cable end Screw clamp terminals 1 flexible AWG 4
Tightening torque	1.7 N.M - on screw clamp terminals 2.2 N.m - on connector
Net weight	0.04 kg

Environment

Product certifications	CE[RETURN]UKCA
------------------------	----------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	6.000 cm
Package 1 Length	7.000 cm
Package 1 Weight	49.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	70
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.706 kg
Unit Type of Package 3	P06
Number of Units in Package 3	1120
Package 3 Height	75.000 cm

Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	69.540 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------