



Main

| | |
|---------------------------|---------------------|
| Range of product | Harmony iPC |
| Product or component type | Flat screen |
| Terminal type | Touchscreen display |
| Device mounting | Flush |

Complementary

| | |
|----------------------------|---|
| Display resolution | 1024 x 768 pixels XGA |
| Display size | 15 inch |
| Aspect ratio | 4:3 |
| Display type | Colour TFT LCD |
| Display colour | 16 million colours |
| Luminance | 400 Cd/M ² 100 cd/m ² |
| Backlight lifespan | 50000 hours |
| Touch panel | Multi touch analogue resistive 1000000 cycles |
| Integrated connection type | DVI-D video port USB 2.0 type A USB 2.0 type mini B |
| Function available | Brightness sensor |
| [Us] rated supply voltage | 12...24 V DC power supply |
| Power consumption in W | 21 W |
| Provided equipment | 1 cable 5 m for DVI-D 1 cable 5 m for USB type A 1 USB cable for mini B USB 2.0 |
| Cut-out dimensions | 383.5 (+ 1/- 0) x 282.5 (+ 1/- 0) mm |
| Depth | 67 mm |
| Height | 296 mm |
| Width | 397 mm |
| Net weight | 5.2 kg |

Environment

| | |
|-------------------------------------|--|
| Standards | UL 508 ANSI/ISA 12-12-01 Class I division 2 CSA C22.2 No 213 CSA C22.2 No 142 |
| Product certifications | ATEX zone 2/22[RETURN]EAC[RETURN]Marine GL Bridge[RETURN]RCM[RETURN]CE |
| IP degree of protection | Front panel: IP67f Front panel: IP66f conforming to UL 50E |
| NEMA degree of protection | NEMA 4X/13 front panel |
| Pollution degree | 2 |
| Ambient air temperature for storage | -20...60 °C |

| | |
|----------------------|---|
| Vibration resistance | 3.5 mm constant amplitude (f = 5...9 Hz) conforming to IEC 61131-2 9.8 m/s ² (f = 9...150 Hz) conforming to IEC 61131-2 |
| Shock resistance | 147 m/s ² conforming to EN/IEC 61131-2 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 30.0 cm |
| Package 1 Width | 39.7 cm |
| Package 1 Length | 59.8 cm |
| Package 1 Weight | 8.494 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |