



Main

Range of product	Harmony GTU
Product or component type	Base unit
Device short name	Premium Box
Range compatibility	Harmony GTU
[Us] rated supply voltage	12...24 V DC power supply

Complementary

Integrated connection type	Ethernet TCP/IP with 2 RJ45 COM1 serial link RJ45 RS485, transmission rate: 110...115200 bit/s COM1 serial link RJ45 RS485, transmission rate: 187.5 kbit/s COM2 serial link SUB-D 9 RS232C/RS422/RS485, transmission rate: 110...115200 bit/s COM2 serial link SUB-D 9 RS232C/RS422/RS485, transmission rate: 187.5 kbit/s Auxiliary port terminal block Expansion unit fieldbus card USB 2.0 port with 2 USB type A USB 2.0 port mini B USB
Communication port protocol	Modbus Uni-Telway Modbus TCP/IP
Operating system	Harmony
Software package	Vijeo Designer run time
Processor name	CPU RISC 600 MHz
Data storage equipment	1 GB SD card
Port Ethernet	10BASE-T/100BASE-TX/1000BASE-T
Memory description	256 MB RAM internal 512 KB NVRAM backup memory
Type of cooling	Natural convection
Width	188 mm
Height	131 mm
Depth	45 mm
Net weight	0.9 kg

Environment

Standards	CSA C22.2 No 142 ANSI/ISA 12-12-01 UL 508 Class I division 2 CSA C22.2 No 213 IEC 61132-2
Product certifications	CE[RETURN]CULus[RETURN]ATEX[RETURN]IEC-Ex[RETURN]RCM[RETURN]GL[RETURN]KCC[RETURN]CUL[RETURN]EAC[RETURN]R[RETURN]
Ambient air temperature for operation	0...60 °C
Ambient air temperature for storage	-20...60 °C
Pollution degree	2 conforming to EN 61131-2 Ed.3

Relative humidity	10...90 % non-condensing
Operating altitude	2000 m
Vibration resistance	3.5 mm constant amplitude (f = 5...9 Hz) conforming to EN/IEC 61131-2 9.8 m/s ² (f = 9...150 Hz) conforming to EN/IEC 61131-2
Electromagnetic compatibility	Electrostatic discharge immunity test level 3 conforming to EN/IEC 61000-4-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	21.0 cm
Package 1 Length	26.0 cm
Package 1 Weight	1.091 kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	4.944 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov