



### Main

|                           |                  |
|---------------------------|------------------|
| Range                     | Vivace           |
| Product or component type | Switched socket  |
| Device short name         | KB15             |
| Device application        | Power supply     |
| Device presentation       | Complete product |
| Switch application        | On/off switching |
| Main colour tint          | White            |
| Colour tint               | White            |

### Complementary

|                              |   |
|------------------------------|---|
| Outlet poles configuration   | 2P + E  |
| Number of gangs              | 1 gang  |
| Colour tint                  | White   |
| Material                     | Polycarbonate: grid plate<br>Polycarbonate: surround<br>Polycarbonate: base |
| Projecting depth             | 8 mm  |
| Device mounting              | Flush   |
| Mounting support             | Wall mounted  |
| Fixing mode                  | By screw M3.5   |
| Fixing center                | 60.3 mm   |
| Embedding depth              | 22.0 mm   |
| Rated current                | 15 A at 250 V AC, resistive   |
| Network frequency            | 50/60 Hz  |
| Contacts material            | Brass and phosphor bronze   |
| Connections - terminals      | Pillar terminal   |
| Terminal identifier          | N<br>Earth<br>L   |
| Tightening torque            | 0.4 N.m   |
| Clamping connection capacity | 2.5 mm <sup>2</sup>   |
| Width                        | 87 mm   |
| Height                       | 87 mm   |
| Depth                        | 35 mm   |

### Environment

|                                       |                               |
|---------------------------------------|-------------------------------|
| Standards                             | MS 589<br>BS 1362-2<br>SS 145 |
| Ambient air temperature for operation | 0...40 °C                     |
| Ambient air temperature for storage   | -5...60 °C                    |
| Relative humidity                     | 0...95 %                      |
| Operating altitude                    | <= 2000 m                     |
| Environmental characteristic          | Indoor use                    |
| IP degree of protection               | IP20                          |

## Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type of Package 1       | PCE |
| Number of Units in Package 1 | 1   |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations      |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|