



Main

Range	Vivace
Product or component type	Power socket-outlet + USB charger
Device presentation	Mechanism
Socket additional information	Shuttered
Colour tint	Aluminium silver
Load type	No inductive load
Type of packing	Plastic bag
Quantity per set	1
Sale per indivisible quantity	1
Type of USB power supply	USB type A + A
Device mounting	Flush
Outlet poles configuration	2P + E with shutter
Rated current	13 A
Colour tint	Aluminium silver

Complementary

Socket number	1
Device mounting	Flush 47 mm
Switch function	ON/OFF power-socket outlet
Number of power socket outlets	1 x 2P + E with shutters, British
Rated current	Power circuit: 13 A 220...250 V, AC, 50/60 Hz
Surface finish	Glossy
Surface treatment	Painted
Number of gangs	1 gang
Connector type	USB type A
[Ue] rated operational voltage	220...250 V AC 50/60 Hz
Maximum power consumption in W	0.075 W
Input power	16 W
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.1 A
Material	Polycarbonate: grid plate Polycarbonate: cover Polycarbonate: surround Polycarbonate: dolly Nylon + GF: shutter Brass: contact plate Steel: spring Steel with Cu plating: terminal screw Copper with silver onlay: bridge
Protection type	USB port: over temperature protection with PWM IC circuit USB port: over voltage protection against surges with PWM IC circuit USB port: overcurrent between output phases and earth (on power up only) with PWM IC circuit
Shape of screw head	Cross
Screwdriver shape	Philips
Electrical connection	3 screw terminal

Clamping connection capacity	1 x 4 mm ² for rigid or stranded cable(s) 2 x 4 mm ² for stranded cable(s) 1 x 2.5 mm ² 2 x 2.5 mm ²
Wire stripping length	10...12 mm
Mounting support	Mounting box conforming to BS 4662
Fixing mode	By screws M3.5 x 25 mm
Fixing center	60.3 mm
Product compatibility	Tablet PC Apple Smartphone XiaoMi Samsung HTC HW Power bank
Height	86 mm
Width	86 mm
Depth	41.9 mm
Embedding depth	30.6 mm
Net weight	0.1 kg
Outlet standard deviation	British
Main colour tint	Aluminium silver

Environment

Operating altitude	<= 2000 m
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Standards	IEC 60950-1 BS 1363-2
Product certifications	IEC
IP degree of protection	IP20
Environmental characteristic	Alcohol Liquid soap

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	105 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	890 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	9.4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information