



## Main

|                               |                                   |
|-------------------------------|-----------------------------------|
| Range                         | Vivace                            |
| Product or component type     | Power socket-outlet + USB charger |
| Device presentation           | Mechanism                         |
| Socket additional information | Shuttered                         |
| Colour tint                   | Aluminium silver                  |
| Load type                     | No inductive load                 |
| Type of packing               | Plastic bag                       |
| Quantity per set              | 1                                 |
| Sale per indivisible quantity | 1                                 |
| Type of USB power supply      | USB type A + A                    |
| Device mounting               | Flush                             |
| Outlet poles configuration    | 2P + E with shutter               |
| Rated current                 | 13 A                              |
| Colour tint                   | Aluminium silver                  |

## Complementary

|                                |                                                                                                                                                                                                                                                   |
|--------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Socket number                  | 1                                                                                                                                                                                                                                                 |
| Device mounting                | Flush 47 mm                                                                                                                                                                                                                                       |
| Switch function                | ON/OFF power-socket outlet                                                                                                                                                                                                                        |
| Number of power socket outlets | 1 x 2P + E with shutters, British                                                                                                                                                                                                                 |
| Rated current                  | Power circuit: 13 A 220...250 V, AC, 50/60 Hz                                                                                                                                                                                                     |
| Surface finish                 | Glossy                                                                                                                                                                                                                                            |
| Surface treatment              | Painted                                                                                                                                                                                                                                           |
| Number of gangs                | 1 gang                                                                                                                                                                                                                                            |
| Connector type                 | USB type A                                                                                                                                                                                                                                        |
| [Ue] rated operational voltage | 220...250 V AC 50/60 Hz                                                                                                                                                                                                                           |
| Maximum power consumption in W | 0.075 W                                                                                                                                                                                                                                           |
| Input power                    | 16 W                                                                                                                                                                                                                                              |
| Integrated connection type     | 2 USB port 5 V DC, maximum load current: 2.1 A                                                                                                                                                                                                    |
| Material                       | Polycarbonate: grid plate<br>Polycarbonate: cover<br>Polycarbonate: surround<br>Polycarbonate: dolly<br>Nylon + GF: shutter<br>Brass: contact plate<br>Steel: spring<br>Steel with Cu plating: terminal screw<br>Copper with silver onlay: bridge |
| Protection type                | USB port: over temperature protection with PWM IC circuit<br>USB port: over voltage protection against surges with PWM IC circuit<br>USB port: overcurrent between output phases and earth (on power up only) with PWM IC circuit                 |
| Shape of screw head            | Cross                                                                                                                                                                                                                                             |
| Screwdriver shape              | Philips                                                                                                                                                                                                                                           |
| Electrical connection          | 3 screw terminal                                                                                                                                                                                                                                  |

|                              |                                                                                                                                                           |
|------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Clamping connection capacity | 1 x 4 mm <sup>2</sup> for rigid or stranded cable(s)<br>2 x 4 mm <sup>2</sup> for stranded cable(s)<br>1 x 2.5 mm <sup>2</sup><br>2 x 2.5 mm <sup>2</sup> |
| Wire stripping length        | 10...12 mm                                                                                                                                                |
| Mounting support             | Mounting box conforming to BS 4662                                                                                                                        |
| Fixing mode                  | By screws M3.5 x 25 mm                                                                                                                                    |
| Fixing center                | 60.3 mm                                                                                                                                                   |
| Product compatibility        | Tablet PC<br>XiaoMi<br>HW<br>HTC<br>Apple<br>Power bank<br>Smartphone<br>Samsung                                                                          |
| Height                       | 86 mm                                                                                                                                                     |
| Width                        | 86 mm                                                                                                                                                     |
| Depth                        | 41.9 mm                                                                                                                                                   |
| Embedding depth              | 30.6 mm                                                                                                                                                   |
| Net weight                   | 0.1 kg                                                                                                                                                    |
| Outlet standard deviation    | British                                                                                                                                                   |
| Main colour tint             | Aluminium silver                                                                                                                                          |

## Environment

|                                       |                          |
|---------------------------------------|--------------------------|
| Operating altitude                    | <= 2000 m                |
| Ambient air temperature for operation | 0...40 °C                |
| Ambient air temperature for storage   | -5...60 °C               |
| Relative humidity                     | 0...95 %                 |
| Standards                             | IEC 60950-1<br>BS 1363-2 |
| Product certifications                | SIRIM[RETURN]IEC         |
| IP degree of protection               | IP20                     |
| Environmental characteristic          | Alcohol<br>Liquid soap   |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 4.2 cm   |
| Package 1 Width              | 8.7 cm   |
| Package 1 Length             | 8.7 cm   |
| Package 1 Weight             | 115.0 g  |
| Unit Type of Package 2       | BB1      |
| Number of Units in Package 2 | 8        |
| Package 2 Height             | 9.5 cm   |
| Package 2 Width              | 15.0 cm  |
| Package 2 Length             | 19.0 cm  |
| Package 2 Weight             | 920.0 kg |
| Unit Type of Package 3       | PAL      |
| Number of Units in Package 3 | 80       |
| Package 3 Height             | 21.0 cm  |
| Package 3 Width              | 31.0 cm  |
| Package 3 Length             | 50.0 cm  |
| Package 3 Weight             | 9.2 kg   |

## Offer Sustainability

|                          |                                                                                                                                 |
|--------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive        | Under investigation                                                                                                             |
| Environmental Disclosure |  <a href="#">Product Environmental Profile</a> |
| Circularity Profile      |  <a href="#">End Of Life Information</a>       |