



## Main

Range	Vivace
Product or component type	Power socket-outlet + USB charger
Device presentation	Mechanism
Socket additional information	Shuttered
Colour tint	White
Load type	No inductive load
Type of packing	Plastic bag
Quantity per set	1
Sale per indivisible quantity	1
Type of USB power supply	USB type A + A
Device mounting	Flush
Outlet poles configuration	2P + E with shutter
Rated current	13 A
Colour tint	White

## Complementary

Socket number	1
Device mounting	Flush 47 mm
Switch function	ON/OFF power-socket outlet
Number of power socket outlets	1 x 2P + E with shutters, British
Rated current	Power circuit: 13 A 220...250 V, AC, 50/60 Hz
Surface finish	Glossy
Surface treatment	Untreated
Number of gangs	1 gang
Connector type	USB type A
[Ue] rated operational voltage	220...250 V AC 50/60 Hz
Maximum power consumption in W	0.075 W
Input power	16 W
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.1 A
Material	Polycarbonate: grid plate Polycarbonate: cover Polycarbonate: surround Polycarbonate: dolly Nylon + GF: shutter Brass: contact plate Steel: spring Steel with Cu plating: terminal screw Copper with silver onlay: bridge
Protection type	USB port: over temperature protection with PWM IC circuit USB port: over voltage protection against surges with PWM IC circuit USB port: overcurrent between output phases and earth (on power up only) with PWM IC circuit
Shape of screw head	Cross
Screwdriver shape	Philips
Electrical connection	3 screw terminal

Clamping connection capacity	1 x 4 mm <sup>2</sup> for rigid or stranded cable(s) 2 x 4 mm <sup>2</sup> for stranded cable(s) 1 x 2.5 mm <sup>2</sup> 2 x 2.5 mm <sup>2</sup>
Wire stripping length	10...12 mm
Mounting support	Mounting box conforming to BS 4662
Fixing mode	By screws M3.5 x 25 mm
Fixing center	60.3 mm
Product compatibility	Apple Samsung Tablet PC XiaoMi HTC Power bank Smartphone HW
Height	86 mm
Width	86 mm
Depth	41.9 mm
Embedding depth	30.6 mm
Net weight	0.1 kg
Outlet standard	British
Main colour tint	White



## Environment

Operating altitude	<= 2000 m
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Standards	IEC 60950-1 BS 1363-2
Product certifications	SIRIM[RETURN]IEC
IP degree of protection	IP20
Environmental characteristic	Alcohol Liquid soap

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	115.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15.0 cm
Package 2 Length	19.0 cm
Package 2 Weight	920.0 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	80
Package 3 Height	21.0 cm
Package 3 Width	31.0 cm
Package 3 Length	50.0 cm
Package 3 Weight	9.2 kg

Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>