



Main

Range	Vivace
Product or component type	Switched socket
Device short name	KB25
Device application	Power supply
Device presentation	Complete product
Switch application	On/off switching
Main colour tint	White
Colour tint	White

Complementary

Outlet poles configuration	2P + E
Number of gangs	2 gangs
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	120.6 mm
Embedding depth	22.0 mm
Rated current	13 A at 250 V AC, resistive
Network frequency	50/60 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	L N Earth
Tightening torque	0.4 N.m
Clamping connection capacity	3 x 2.5 mm ² 2 x 4 mm ²
Width	147 mm
Height	87 mm
Depth	35 mm

Environment

Standards	SS 145 MS 589 BS 1362-2
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Operating altitude	<= 2000 m

Environmental characteristic	Indoor use
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	168 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------