



## Main

Range	Vivace
Product or component type	USB charger
Device application	Power supply
Type of USB power supply	USB type A + C
Colour tint	Wall: aluminium silver
Fixing mode	Screw

## Complementary

Socket number	2
Device mounting	Flush
Device presentation	Complete product
Range compatibility	Vivace
Colour tint	Aluminium silver
[Ue] rated operational voltage	100/240 V AC at 50/60 Hz
Surface finish	Painted
Connections - terminals	Screw terminal
Surface treatment	Painted
Number of terminals	2
Number of modules	1 module 54.8 x 51.5 x 38.7 mm
Nominal output power	21 W
Type of packing	Plastic bag
Quantity per set	1
Sale per indivisible quantity	1
Condition of use	Room temperature
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Power consumption in W	21 W
Output voltage	5 V DC, 3 A
Integrated connection type	2 USB port 5 V DC, maximum load current: 3 A USB port 9 V, maximum load current: 2.1 A USB port 12 V, maximum load current: 1.5 A
Maximum load current with 2 outputs used simultaneously	3 A
Material	PC (polycarbonate): surround PC (polycarbonate): grid plate PA (polyamide) 6: housing Silicone rubber: cover
Shape of screw head	Cross
Number of terminals	2 screw terminals
Clamping connection capacity	2.5 mm <sup>2</sup> for stranded cable(s) 2.5 mm <sup>2</sup> for solid cable(s) 1.5 mm <sup>2</sup> for stranded cable(s) 1.5 mm <sup>2</sup> for solid cable(s)

Wire stripping length	10 mm
Product compatibility	HTC XiaoMi Apple Samsung HW Major smart phone and tablet
Standards	MS IEC 60950-1:2007 IEC 60950-1 IEC 62368-1 IEC 61558-2-16
Height	87 mm
Width	87 mm
Depth	38.3 mm
Embedding depth	29.7 mm
Net weight	0.118 kg
Main colour tint	Aluminium silver






## Environment

Product certifications	IEC
IP degree of protection	IP20
Environmental characteristic	Petrol

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	124 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	992 g
Unit Type of Package 3	PAL
Number of Units in Package 3	1600
Package 3 Height	110 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	220.4 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>

Contractual warranty

Warranty	1 Year
----------	--------