



Main

Range of product	Vivace
Range	Vivace
Device short name	KB33
Product or component type	TV/FM/SAT socket
TV socket type	TV/FM/SAT
Device presentation	Complete mechanism

Complementary

Number of gangs	1 gang
Number of outputs	1
Connector type	M-110 keystone RJ45 connector
Material	Polycarbonate: surround Polycarbonate: grid plate
Maximum insertion loss	2 DB (+/- 1.5 dB) at 88...125 MHz (IN-FM) 1 DB (+/- 1.5 dB) at 40...70 MHz (IN-TV) 2 DB (+/- 1.5 dB) at 174...862 MHz (IN-TV) 2 DB (+/- 1.5 dB) at 950...2150 MHz (IN-SAT) 2 dB (+/- 1.5 dB) at 2150...2400 MHz (IN-SAT)
Minimum return loss	5 DB 40...2400 MHz IN 8 DB 87.5...125 MHz FM-SAT 5 DB 40...862 MHz TV 5 dB
Isolation	20 dB at 88...108 MHz (TV-FM) 6 dB at 40...2400 MHz (TV-SAT) 30 dB at 40...860 MHz (FM-SAT)
TV connector	Male IEC
Radio connector	Male IEC
SAT connector	Female F type
Average impedance	75 Ohm
Projecting depth	36.2 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Colour tint	White
Embedding depth	35 mm
Connections - terminals	Cable terminal
Tightening torque	0.4 N.m
Width	86 mm
Height	86 mm
Net weight	110 g
Main colour tint	White

Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	No exposure to direct radiation from sunlight

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	153.75 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.8 cm
Package 2 Width	15.1 cm
Package 2 Length	19.1 cm
Package 2 Weight	1230 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	20.5 cm
Package 3 Width	41.5 cm
Package 3 Length	50 cm
Package 3 Weight	12164 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------