



Main

Range	TeSys
Device short name	LT6CT
Product or component type	Current transformer
Range compatibility	TeSys TeSys T motor controller

Complementary

Current transformer ratio	100/1
Accuracy class	Class 5P
Precision limit factor	15
[Ui] rated insulation voltage	690 V
Diameter	35 mm
Cable cross section	300 mm ²
Height	107 mm
Width	95 mm
Depth	25 mm
Net weight	0.55 kg

Environment

Standards	IEC 60185 BS 7626
Maximum ambient air temperature for operation	50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	12.5 cm
Package 1 Length	10.6 cm
Package 1 Weight	530.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	11.05 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------