



### Main

|                           |                         |
|---------------------------|-------------------------|
| Range                     | TeSys                   |
| Device short name         | LU9R                    |
| Product or component type | Line terminator 120 Ohm |

### Complementary

|                     |             |
|---------------------|-------------|
| Range compatibility | TeSys Ultra |
|---------------------|-------------|

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 2.0 cm   |
| Package 1 Width              | 5.0 cm   |
| Package 1 Length             | 5.0 cm   |
| Package 1 Weight             | 10.0 g   |
| Unit Type of Package 2       | BAG      |
| Number of Units in Package 2 | 50       |
| Package 2 Height             | 7.0 cm   |
| Package 2 Width              | 16.0 cm  |
| Package 2 Length             | 30.0 cm  |
| Package 2 Weight             | 555.0 g  |
| Unit Type of Package 3       | S03      |
| Number of Units in Package 3 | 500      |
| Package 3 Height             | 30.0 cm  |
| Package 3 Width              | 30.0 cm  |
| Package 3 Length             | 40.0 cm  |
| Package 3 Weight             | 6.306 kg |

### Offer Sustainability

|                            |                                                                                                                             |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                           |
| REACH free of SVHC         | Yes                                                                                                                         |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>                                                                               |
| Toxic heavy metal free     | Yes                                                                                                                         |
| Mercury free               | Yes                                                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                      |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                         |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|