



Main

Range	MasterPact
Device short name	OF[RETURN]micro switch[RETURN]PF[RETURN]SDE
Product or component type	Auxiliary contact block
Device application	Control
Range compatibility	Masterpact MasterPact MTZ2 circuit breaker Masterpact MasterPact MTZ3 circuit breaker

Complementary

Auxiliary contacts type	Standard
Signal contacts composition	4 NO/NC
Breaking capacity	6 A AC-12 240/380 V AC 50/60 Hz 2 A AC-12 480 V AC 50/60 Hz 0.3 A DC-12 125 V DC 0.15 A DC-12 250 V DC 3 A AC-12 690 V AC 50/60 Hz
Minimum load	100 mA at 24 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	8 cm
Package 1 Length	8 cm
Package 1 Weight	20 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	6 cm
Package 2 Width	18 cm
Package 2 Length	26.5 cm
Package 2 Weight	222 g
Unit Type of Package 3	S03
Number of Units in Package 3	64
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2.176 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov