

Main

Range	MasterPact
Product or component type	Ethernet interface module
Condition of use	With specific accessories
Device application	Communication
Device mounting	Embedded

Complementary

Communication gateway	Ethernet TCP/IP to Modbus
Communication network type	ULP, CANopen on USB Ethernet, Ethernet TCP/IP10/100 Mbps on RJ45
Circuit breaker mounting mode	Drawout
Mounting support	DIN rail
Localisation on device	Chassis
Maximum supply current	3 A
Power consumption in W	72 W
Product certifications	FCC[RETURN]CE[RETURN]EAC
Standards	IEC 60947-6-2 IACS E10 IEC 60950
Height	51 mm
Width	51 mm
Depth	52.5 mm
Net weight	0.075 kg
Web server	Embedded

Environment

IP degree of protection	IP30
Ambient air temperature for operation	-20...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.0 cm
Package 1 Length	8.2 cm
Package 1 Weight	172.0 g

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
SCIP Number	1fcd1b36-362e-41d8-9b56-5633867871a1
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Halogen content performance	Halogen free plastic parts product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	93