



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Side panel
Accessory / separate part category	Enclosure accessory Spare part
Range compatibility	PrismaSeT PrismaSeT G enclosure
Installation description	Wall-mounted enclosure
Mounting location	Side
Number of vertical modules [50 mm]	12

Complementary

Material	Treated sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Matt Textured
Colour	White (RAL 9003)
Width	195 mm
Height	625 mm
Depth	45 mm
Net weight	1.3 kg
Quantity per set	Set of 1

Environment

IP degree of protection	IP30
IK degree of protection	IK08

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	20.5 cm
Package 1 Length	68.0 cm
Package 1 Weight	1.367 kg
Unit Type of Package 2	P12
Number of Units in Package 2	30
Package 2 Height	40.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	52.5 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product