

LVS01051

Plinth spare part, PrismaSeT G, 2 plain base brackets (left/right) with screws, for IP30 enclosure



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Bracket
Accessory / separate part category	Spare part
Range compatibility	PrismaSeT PrismaSeT G enclosure
Product compatibility	IP43 enclosure IP31 enclosure IP30 enclosure
Provided equipment	4 self-threading screws 1 right base bracket 1 left base bracket

Complementary

Installation description	Floor-standing enclosure Floor-standing duct
Quantity per set	Set of 1
Height	150 mm
Net weight	1 kg
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.0 cm
Package 1 Width	21.2 cm
Package 1 Length	30.6 cm
Package 1 Weight	1.528 kg
Unit Type of Package 2	P12
Number of Units in Package 2	80
Package 2 Height	97.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	134.0 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations