



### Main

Range	PrismaSeT
Range of product	PrismaSeT G PrismaSeT G Active
Product or component type	Central upright
Accessory / separate part category	Enclosure accessory Spare part
Range compatibility	PrismaSeT PrismaSeT G enclosure
IP degree of protection	IP30
Accessory / separate part destination	For side by side framework combination

### Complementary

Installation description	Wall-mounted enclosure - width 600 mm Wall-mounted enclosure - width 300 mm
Number of vertical modules [50 mm]	18
Mounting location	Side by side
Quantity per set	Set of 1
Height	930 mm
Surface finish	Matt Textured
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	20.0 cm
Package 1 Length	113.0 cm
Package 1 Weight	1.236 kg
Unit Type of Package 2	P12
Number of Units in Package 2	12
Package 2 Height	33.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	28.0 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes

Sustainable packaging	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product