



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Metering panel kit
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Type of front plate	Cut-out
Installed device	Resi9: by screws DB 90 - control: toggle - vertical installation Power meters: kilowatt-hour meters - vertical installation
Poles description	1 x 1P + N: mounting plate support: DB 90 vertical installation 1 x 1P + N: mounting plate support: kilowatt-hour meters vertical installation

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Pack enclosure - width 555 mm
Number of vertical modules [50 mm]	6
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASTA
Material	Steel
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	300 mm
Net weight	4.68 kg
Quantity per set	Set of 1
Functional unit	600 mm PrismaSeT G floor-standing enclosure Resi9 DB 90 by screws toggle vertical 1P + N 1 50 mm 600 mm PrismaSeT G wall-mounted enclosure Resi9 DB 90 by screws toggle vertical 1P + N 1 50 mm 600 mm PrismaSeT G floor-standing enclosure power meters kilowatt-hour meters vertical 1P + N 1 50 mm 600 mm PrismaSeT G wall-mounted enclosure power meters kilowatt-hour meters vertical 1P + N 1 50 mm

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	32.0 cm
Package 1 Length	55.0 cm

Package 1 Weight	4.761 kg
Unit Type of Package 2	P12
Number of Units in Package 2	24
Package 2 Height	79.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	125.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes