



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Installed device	Power meters: kilowatt-hour meters - vertical installation connection
Poles description	2 x 4P: kilowatt-hour meters vertical installation
Number of vertical modules [50 mm]	6 module(s): kilowatt-hour meters in 600 mm Widefloor-standing enclosure 6 module(s): kilowatt-hour meters in 600 mm Widewall-mounted enclosure 6 module(s): connection in 600 mm Widefloor-standing enclosure 6 module(s): connection in 600 mm Widewall-mounted enclosure
Standards	IEC 61439-2
Product certifications	ASTA

Complementary

Material	Sheet steel
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Textured Matt
Colour	White (RAL 9003)
Width	600 mm
Height	300 mm
Net weight	1.5 kg
Functional unit	600 mm PrismaSeT G floor-standing enclosure connection 2 6 50 mm 600 mm PrismaSeT G wall-mounted enclosure connection 2 6 50 mm 600 mm PrismaSeT G floor-standing enclosure power meters kilowatt-hour meters vertical 4P 2 6 50 mm 600 mm PrismaSeT G wall-mounted enclosure power meters kilowatt-hour meters vertical 4P 2 6 50 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	27.0 cm
Package 1 Length	47.0 cm
Package 1 Weight	1.526 kg
Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm

Package 2 Length	60.0 cm
Package 2 Weight	15.883 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	72.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	140.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product