



## Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing enclosure - width 850 mm
Mounting plate description	Flat slotted
Number of vertical modules [50 mm]	4 module(s) in 600 mm Widefloor-standing enclosure 4 module(s) in 600 mm Widewall-mounted enclosure 4 module(s) in 850 mm Widefloor-standing enclosure
Standards	IEC 61439-2
Product certifications	ASTA

## Complementary

Material	Steel
Surface finish	Galvanized
Width	600 mm
Height	200 mm
Net weight	0.72 kg
Functional unit	600 mm PrismaSeT G floor-standing enclosure 4 12.5 mm 600 mm PrismaSeT G wall-mounted enclosure 4 12.5 mm 850 mm PrismaSeT G floor-standing enclosure 4 12.5 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.200 cm
Package 1 Width	19.400 cm
Package 1 Length	47.000 cm
Package 1 Weight	750.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	8.074 kg
Unit Type of Package 3	P12
Number of Units in Package 3	120
Package 3 Height	106.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	108.000 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product