



Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Mounting plate description	Recessed slotted
Installed device	Phaseo: LV/LV transformer
Number of vertical modules [50 mm]	4 module(s): LV/LV transformer in 600 mm Widefloor-standing enclosure 4 module(s): LV/LV transformer in 600 mm Widewall-mounted enclosure
Standards	IEC 61439-2
Product certifications	ASTA

Complementary

Material	Steel
Surface finish	Galvanized
Width	600 mm
Height	200 mm
Net weight	0.74 kg
Functional unit	600 mm PrismaSeT G floor-standing enclosure Phaseo LV/LV transformer 4 12.5 mm 600 mm PrismaSeT G wall-mounted enclosure Phaseo LV/LV transformer 4 12.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	18.5 cm
Package 1 Length	46.5 cm
Package 1 Weight	731.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	7.918 kg
Unit Type of Package 3	P12
Number of Units in Package 3	120
Package 3 Height	108.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	108.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product